

Bluefin Pigmores Thx Ultra G06

3537

High-quality, water-based pigment paint, can be applied directly onto MDF, for **furniture and interior finishing, for use in industry and trade**

PRODUCT DESCRIPTION

General

Water-based 2C pigment paint for furniture, for high-quality furniture surfaces with very good filling performance and sandability, very good chemical and mechanical resistance, good ring test resistance and excellent stability on vertical surfaces. The product is resistant to cream and grease. Can be applied directly onto MDF boards (please read the information to follow: "MDF boards"!). Bluefin Pigmores Thx Ultra G06 fulfils the functions of insulator, filler, coloured paint and spray-on paint.

Special properties and standards



- **ÖNORM A 1605-12 (furniture surfaces)**
Resistance to chemical reactions: 1-B1
Response to abrasion: 2-D (≥ 50 U)
Response to scratches: 4-D (≥ 1.0 N)
Flame treatment: 5-B (hardly inflammable furniture surface)



- **DIN 68861 (furniture surfaces)**
Part 1: Response to chemical stress: 1 B
Part 2: Response to Abrasion: 2 D (> 50 to ≤ 150 U)
Part 4: Response to scratches: 4 D ($> 1,0$ to $\leq 1,5$ N)



- **ÖNORM A 3800-1 (fire behaviour)**
In conjunction with a flame-retardant substrate:
flame-retardant, Q1, Tr 1



- **DIN 53160-1 and DIN 53160-2**
Perspiration and saliva-proof properties



- **ÖNORM EN 71-3**
Safety of toys; migration of certain elements (free of heavy metals)



- **Declared in baubook**
Product has been declared and validated




- **French ordinance DEVL1104875A**
Marking of construction coating products for their emission of volatile pollutants: A+

2-0 IMC 3537 | 08/25 | replaces 1-0

ADLER-Werk Lackfabrik, A-6130 Schwaz

Fon: +43/5242/6922-190, Fax: +43/5242/6922-309, Mail: technical-support@adler-lacke.com


Our instructions are based on the current state of knowledge and are intended to advise the buyer/user to the best of our knowledge, but must be individually adapted to the areas of application and processing conditions. The buyer/user is responsible for deciding on the suitability and use of the supplied product, which is why we recommend that a sample be produced to check the suitability of the product. In all other respects, our General Terms and Conditions of Sale apply. All previous data sheets lose their validity with this edition. We reserve the right to make changes to container sizes, color shades and available gloss levels.

Application area

For the coating of furniture and interior finishing exposed to high levels of stress, such as tabletops and shelves in the kitchen and living area, bathrooms, offices and in the contract sector, fronts and permanently visible areas, surfaces used on seating furniture and not permanently visible areas. Application areas II to IV in accordance with ÖNORM A 1610-12.

For effective coating of MDF boards using the so-called "varnish on varnish" method: with 2 or 3 applications of Bluefin Pigmores Thx Ultra G06 (3537), you can achieve a rich and substantial surface with very good ring test resistance on MDF boards.

For hardly inflammable or flame-retardant coating systems.

PROCESSING**Processing instructions**

- Please stir the product before use.
- The temperature of the product and object, and the room temperature must be at least + 15 °C.
- When using plastic edgebands, an adhesion test must always be carried out with the planned structure. Adhesion can be improved on ABS edgebands by using ABS Kantenaktivator (8315000210).
- Any change in the processing sequence, environmental conditions, non-observance of instructions or the use of products not listed may have an unfavourable effect on the result.
- Please follow our **ARL 150 - Working guidelines for water-based furniture coatings**.

Blending ratio

100 Part(s) by weight Bluefin Pigmores Thx Ultra G06 (3537)
10 Part(s) by weight Aqua-Hardener 8452 (8452000210)

Aqua-Hardener 8452 (8452000210) must be carefully worked into the product by stirring before processing. We recommend waiting approx. 10 minutes before starting work.

Bluefin Pigmores Thx Ultra G06 (3537) can only be used with a hardener and in the mixing ratio specified. Deviations lead to film and adhesion problems.

Pot life

5 hour(s)

Increased temperatures reduce the pot life. A further extension of the pot life is not possible.

Application technique

	Airless	Airless air-supported (Airmix®, Aircoat, etc.)	Cup gun
Spraying nozzle Ø (mm)	0,23 - 0,33		2,0
Spraying pressure (bar)	100 - 120		2 - 3
Vaporizer Air (bar)	-	1 - 2	-
Applied quantity per application (g/m ²)	120 - 200*		
Total quantity applied (g/m ²)	max. 450		

*closed-pore surfaces: approx. 130
open-pore coating systems in pastel shades and RAL 9010: approx. 150 – 200
open-core coating systems in solid colours approx. 120 – 150

The product is ready to use.

Drying times

(at 23 °C and 50 % rel. humidity)



Sandable and recoatable:

approx. 5 hour(s)

In order to improve the firmness of the subsequent coating, we recommend drying overnight at room temperature.

The mentioned system parameters are reference values, which must be coordinated with the respective plant. Drying depends on the substrate, layer thickness, temperature, air exchange, relative humidity, stacking pressure and stacking conditions.

Cleaning the working equipment

8029

With water immediately after use.

To remove dried paint residues we recommend using Aqua-Cleaner (8029) (diluted 1:1 with water).

SUBSTRATE**Type of substrate**

Carrier plates coated with priming film
MDF panels

Substrate property

The substrate must be dry, clean, capable of holding the paint, free from separating substances such as grease, wax, silicone, etc. and free from dust, as well as tested for suitability for coating.

Substrate preparation**Carrier plates coated with priming film:**

Film sanding Grit size 220 – 240

MDF panels:

Cleaning/smoothing sanding grit size 180 - 220

On good quality MDF boards with a high bulk density (e.g. with 19 mm boards exceeding 700 kg/m³) Bluefin Pigmores Thx Ultra G06 (3537) can be applied directly, without preinsulation. Boards of a lesser quality will need to be pre-insulated before the first coat of primer (e.g. with Bluefin Top-Antiscratch (2960)).

For applications in the sanitary sector, we generally recommend the use of moisture-resistant MDF boards of type P3, P5 or P7 in accordance with ÖNORM EN 312 (formerly V100 in accordance with DIN 68763) with pre-insulation. It is not recommended for use on horizontal surfaces that are frequently exposed to water, such as washstands.

COATING SYSTEM**Primer coat**

1 - 3 x Bluefin Pigmores Thx Ultra G06 (3537), depending on the desired substrate and body.

Drying overnight at room temperature.

Intermediate sanding

Grit size 280 – 360

Intermediate sanding must be carried out immediately before the subsequent coating is applied in order to ensure good intermediate adhesion!

Avoid sanding straight through!

Topcoat

1 x Bluefin Pigmores Thx Ultra G06 (3537)

CLEANING AND MAINTENANCE

Cleaning and Maintenance Cleaning with Clean-Möbelreiniger (7202) and care with Clean-Möbelpflege Plus (7222).

ORDERING INFORMATION

Size of trading unit 4 kg, 20 kg

Colour shades / Glosslevels Bluefin Pigmores Thx Ultra G06 (3537) & colour number
RAL colours, NCS colours and special colours can all be supplied.

Supplementary products ABS Kantenaktivator (8315)
Aqua-Cleaner 8029 (8029)
Aqua-Hardener 8452 (8452)
Bluefin Top-Antiscratch (2960)
Clean-Möbelpflege Plus (7222)
Clean-Möbelreiniger (7202)

Please refer to the corresponding technical data sheets of the products.

FURTHER DETAILS

Durability / storage



Min. 9 month(s) in the original sealed containers.

Cool, but frost-free.

Close opened containers well and use up the content as soon as possible.

Technical specifications

Delivery viscosity: 150 – 160 seconds according to DIN 53211
(4 mm measuring cup, 20 °C)

Safety information



The product is only suitable for the industrial and professional use.

The inhalation of paint aerosols during spray application must generally be avoided. This is ensured by the proper use of a respirator (combination filter A2/P2).

Further information on the subject of safety during transport, storage and handling as well as disposal can be found in the relevant safety data sheet. The current version can be accessed on the Internet at www.adler-lacke.com.